# Aseptic and Hygienic Filling

# Filling & Sealing the processed product into Multi-packaging

### Complete FS Filling range

FS211 Clean-Fill ESL



ESL Extended Shelf Life Filler Cost effective solution to fill and seal sterilized product into multiple containers in a hygienic controlled environment.

Suitable for CIP & SIP

FS211
Clean-Fill ESL Extended



ESL Filler Extended Edition

The extended edition makes more space for containers. A second filling point enables faster throughput to pack processed samples.

Suitable for CIP & SIP

FS212 Asepto-Fill®



Isolator Technology

Glove box, built in HEPA filter with presterilized isolated environment. The system uses decontaminated (gamma-radiated) containers and caps for secure filling/capping.

Suitable for CIP & SIP

FS205

Flexi-Fill Counter-Pressure Filler



Industrial Filling sequence for sodas Carbonated drinks can easily be packed in multiple types of containers.

Suitable for liquids with/without particles and fibers.

FS218
Aseptic Bag Filler



Dynamic Bag Filler Modular built system Buffering, Filling and sealing

Buffer tank capacity 20L, more on request



# Successfully Test Your Product Packaging

Endless possibilities to show your new formula

Standard & custom-made systems for your application and process needs

## Sealers/Closures













- Bottle up
- Flush bottle with CO2
- Pressurize bottle
- Filling
- Depressurize bottle
- Closing bottle
- Bottle down

All steps are fully customizable in HMI Touch screen



Heat sealer

device

**CUPS** Closing with aluminum lids



Crown

capper

**GLASS** Filling & closing crown cork



Screw

capper

Filling & closing screw caps



**CANS** Filling & seaming

### Compatibility

FS205 available filling & closing

Pack your product in



Aseptic Bags From 5L to 200

Higher capacities on request

Complete HTST/UHT process with products packed in Aseptic Filler





Tel +31 302 410 070 Fax +31 302 411 936 sales@omve.com www.omve.com

